



Flip your expectations.

The Flip miniRIC provides all of the features patients want most: simple operation, wireless connectivity, and a size that's stylish and discreet—all with the outstanding sound quality Sonic is known for. It's everything most people with hearing loss need to enjoy the flip side of life.

Natural Sound Made Simple.

Built on the solid foundation of the Speech Variable Processing Technology Platform, Flip gives patients a natural listening experience. Sophisticated Speech Priority Noise Reduction keeps conversations clear, and wireless binaural features provide simple operation.

Stay Connected with Life

Created specifically to adapt to today's technologies, Flip comes ready to connect to nearly any external device.

A Size and Style to Flip For

Flip is small. People love that about this discreet device. They also love that it's smart. While compact in size, Flip doesn't short-change any features. Push buttons are simple to find and easy to use. A sizeable wheel makes volume control easy. And the size 13 battery provides weeks of battery life while being super easy for patients to manipulate.

ACOUSTIC PERFORMANCE

		Power Receiver		Standard Receiver	
		2cc	Ear Sim	2cc	Ear Sim
OSPL 90, peak	dB SPL	120	131	110	121
OSPL90, 1600 Hz	dB SPL	119	129	107	115
HFA OSPL 90	dB SPL	116	-	107	-
Full-on Gain, peak	dB	60	70	48	59
Full-on Gain, 1600 Hz	dB	58	67	45	53
HFA Full-on Gain	dB	54	-	45	-

FEATURE OVERVIEW

	Flip 100	Flip 80	Flip 60	Flip 40
Sound Quality				
Signal Processing	◀ Speech Variable Processing ▶			
Frequency Bandwidth	10 kHz	8 kHz	8 kHz	8 kHz
Noise Management				
Adaptive Feedback Cancellor	■	■	■	■
Wind Noise Reduction	■	■	■	■
Soft Noise Reduction	■	■	■	■
Speech Priority Noise Reduction	4 levels	3 levels	2 levels	2 levels
Impulse Noise Reduction	■	■		
Directionality				
Fixed	■	■	■	■
Adaptive	■	■	■*	
Hybrid Directionality	■			
Binaural Coordination				
Volume & Program Change	■	■	■	
Environment Classification	■	■		
Non-Telephone Ear Control (with Auto Telephone)	■			
Programming Options				
Universal Program	■	■	■	■
Manual Listening Programs	4	4	3	3
Environments	13	10	8	4
Data Logging	■	■	■	■
Data Learning	■			
Wireless Programming	●	●	●	
Patient Conveniences				
Push Button Mute	■	■	■	
Audible Performance Indicators	■	■	■	■
Start-Up Delay	■	■	■	■
Auto Telephone Detection	■	■	■	

* MNRx only

■ STANDART ● OPTIONAL

MODEL OVERVIEW



Flip miniRIC

Battery	13
Estimated Battery Life (in hours)	238 (Standard) 112 (Power)
Program Button	■
Directionality	■
Telecoil	■
Auto Telephone	■
RIC Fitting	■
Receiver Options	Standard Power
Wireless Accessories	● *

* Accessories for Flip 100 | 80 | 60 only

■ STANDART ● OPTIONAL

Color Options:



beige



dark brown





black



grey

FITTING RANGES



ACOUSTIC OPTIONS

Instant Fit

Custom Fit

Instant Fit		S	M	L	Custom Fit
Standard Receiver	Open Dome	■	■	■	Custom Mold
	Tulip Dome	Universal Size			
	Power Dome	■	■	■	
Power Receiver	Power Dome	■	■	■	Power Mold
	Tulip Dome	Universal Size			